

FOUNT TR

PREMIUM FOUNTAIN SOLUTION FOR WEB PRESSES

The Product

Fount TR is a premium high performance Fountain Solution for Web Presses.

Features

- Helps keep the dampening rollers clean and free from ink.
- Contains ingredients which prevent oxidation of plate.
- Contains a very special gum agent. This avoids the need to gum the plates during short press stop.
- Strong buffer maintains the pH value at constant while printing.
- Contains anti-piling properties to reduce press downtime.

User Guidelines

- Recommended to use 2% dilution of Fount TR with pH ranged between 4.8 - 5.2
- Thoroughly clean and deglaze the inking rulers and dampening rubber rollers.
- Charge the freshly mixed solution and use a freshly calibrated meter, for accurate dosing control.
- Thoroughly clean the dosing, circulation and feeding systems with Fount System Cleaner.

Safety & Security

- Always make use of Protective gloves and goggles (eye wear) while using the Fountain Solution.
- Keep container closed when not in use.
- Store separately in a cool and dry storage area. The storage area must be aptly ventilated.
- Avoid direct skin and eye contact. Do not inhale the vapours / fumes directly.
- In case of Skin / Eye contact immediately rinse with water thoroughly and consult a physician.
- In case of ingestion immediately consult a physician. - Do not induce vomiting.

Available In

- | | | |
|------------|--------------|--------------|
| ● 200 L | ● 20 / 25 L | ● 5 L |
| Steel Drum | Plastic Cont | Plastic Cont |

FOUNTAIN SOLUTIONS